




### Main

Range	KNX
Aesthetic name	D-Life System Design
Product or component type	Presence detector
Bus type	KNX
Colour tint	Sahara

### Complementary

Device presentation	Mechanism with central plate
Number of channels	5
Protection type	Creep zone protection
Type of setting	Light sensitivity adjustable
Duty cycle	15300 minutes
Time delay range	0...1 s (switch-on)
Detection face	Lateral: 8 m
Detection angle	180° horizontal
Material	Polycarbonate
Surface treatment	Varnished
Device mounting	Flush
Mounting height	2.2 m

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>