



ENGLISH

Datasheet

Automatic Steel 900W Hand Dryer, 175mm x 277mm x 201mm

RS Stock 711-2591



Specifications

Designed to provide low cost effective alternative to conventional hand dryers and paper towels. These new dryers have been developed with speed in mind. They provide rapid drying times of 10 seconds, almost half that of the competitors products, thus reducing washroom time. They are also 70% energy saving when compared to conventional dryers.

Automatic hand dryer for heavy duty applications - 10-15 second drying time.

- Unique "blue dry zone" indicator
- Cover: Steel. Finish porcelain enamel coating
- Insulation Earthed Class 1
- 201 x 277 x 175 (WxHxD)
- Weight 6.6kg (packaged)
- Air flow 116m³/h
- Heater Element 450-900W, adjustable
- Infrared automatic operation
- 60 second auto shut off