




TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



CARRYVOLT PORTABLE VARIABLE TRANSFORMER

MODEL: CMCTV10
INPUT: 230-240V
OUTPUT: 0-112% OF INPUT
RATING: 10A MAXIMUM
FUSE: 10A
VOLTMETER: 0-300V
AMMETER: 0-10A
INPUT LEAD: 2m 15A 3-CORE CABLE WITH
 BS1363 13A UK DOMESTIC PLUG
SOCKETS: BS1363 13A UK DOMESTIC SOCKET
 IEC60320 10A APPLIANCE SOCKET
 4mm DIAMETER ROUND TEST SOCKETS

REV	
4	
3	
2	
1	

CARROLL & MEYNELL
 TRANSFORMERS LIMITED
 TEL: 01642 617406 FAX: 01642 614178
 enquiries@carroll-meynell.com

TITLE
 CARRYVOLT
 CMCTV10
 ALL DIMENSIONS IN mm

DRAWN	PROJECTION	DATE	SCALE
GB		15/02/08	NTS
DRAW No	REV	PAGE	
5086	0	1/1	