

Product datasheet

Specifications



Universal Mounting Accessory, XV4/ XV6/XVB7 Modular Tower Light, Plastic Fixing Plate With Pole, Silver

XVZ02Q

Main

Product or component type	Accessory
Accessory / separate part type	Plastic fixing plate with pole
Product compatibility	XVB7..... XV6..... XV4.....
Material	Plastic
Provided accessory	Gasket
Product weight	0.081 kg

Complementary

Height	112 mm
cable entry	Bottom entry
Colour	Silver

Environment

IP degree of protection	IP66
Environmental Type ratings	Type 4/4X/12/13 indoor use only

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.400 cm
Package 1 Width	7.500 cm
Package 1 Length	13.600 cm
Package 1 Weight	64.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.421 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	1 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.9 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	80
End of life manual availability	End of Life Information
Take-back	No

Offer Marketing Illustration

Product benefits / Features

Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits
Harmony XVB7

Conformity with IEC, CUL and CCC standards, as well as CE marking

Up to IP66 and type 4X protection ratings

High shock and vibration resistance up to 6g



Energy efficient LED with operating life up to 50,000 hours

Save up to 75% wiring time with M12 connection and push-in terminal

High brightness level with illuminance up to 3000cd/m2

Image of product / Alternate images

Alternative





