

| | |
|-------------|--|
| Description | High quality polyester fabric tape coated with a strong rubber adhesive. This product is hand tearable. |
| Application | Used for cable harnessing in the automotive, vehicle and aerospace industry. |
| Features | Wide temperature range High abrasion resistance Very good adhesive properties High media resistance Stable against rotting Flexible and easy to handle Free of critical substances |



Technical Data

| Material | Polyester Fabric | Test method |
|--------------------------------|--|-------------|
| Colour | black | |
| Thickness (carrier) | 0.18 mm | EN 1942 |
| Core Ø | 38 mm | |
| Adhesive base | rubber adhesive | |
| Adhesion to steel | 3.0 N / 10mm | EN 1939 |
| Adhesion to backing | 3.0 N / 10mm | EN 1939 |
| Unwind resistance | 3 N / 10 mm | EN 1944 |
| Tensile strength | 65 N / 10mm | EN 14410 |
| Elongation | 15 % | EN 14410 |
| Temperature resistance | -40°C up to +125°C | LV312 |
| Storage life | 24 month | |
| Recommended storage conditions | Relative humidity: 65% Room temperature: 23°C | |