

Features

- 7.62mm pitch
- Voltage Rating: 300V
- Current Rating: 15A
- Low Mating Force
- 6 WAY HEADER
HORIZONTAL
TERMINAL

RS PRO 7.62MM PITCH 6 WAY, 15A, HEADER HORIZONTAL TERMINAL

RS Stock No.: 0631122



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Right angle mount closed end PCB terminal block headers with a 7.62mm pitch. These 7.62mm pluggable terminal block PCB header connectors have a 300V 15A electrical rating and green PA66 housings

General Specifications

Number of Contacts	6
Number of Rows	1
Pitch	7.62mm
Mounting Type	Through Hole
Body Orientation	Right Angle
Number of P	6
Termination Method	Solder
Contact Material	Brass
Contact Plating	Tin plated
Housing	PA66(UL94V-0)
Colour	Green

Electrical Specifications

Voltage Rating	300V
Current Rating	15A
Insulation Resistance	500M ohm min
Withstanding Voltage	2500V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	7.62 mm
Pin size	Please see below drawings
Pin height	3.7mm

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, UL, CE
Declarations	Reach

Spec Drawings

