



RS Pro 10mm Screwed Shank End Mill BS 122/4

RS Stock No: 2348278





Specifications:

4 Flute Screwed Shank End Mill Centre Cutting BS 122/4

High Speed Steel: M35 with 5% Cobalt

| Order Code | Manufacturers Code | Product Description |
|------------|-----------------------|-----------------------------|
| | 2348278 | 10mm Screwed Shank End Mill |





Datasheet RS Pro 10mm Screwed Shank End Mill BS 122/4

Technical Specifications:

| Code | Dia mm | Flute Lgth | O/A Lgth. | Shank Dia |
|------|--------|------------|-----------|-----------|
| | 10.0 | 21.0 | 66.5 | 10.0 |