



FLAMESTAT HIGH VIS CRAFTSMAN TROUSERS WOMAN CLASS 2 2775 ATHS

ART. NO: 122196

Dirt, oil and water repellent / Concealed front button / 2 CORDURA® reinforced, loose-hanging front pockets, left pocket with extra pocket and right pocket with 3 pockets and tool loops / 2 front pockets / 2 CORDURA®-reinforced back pockets one with flap / D-ring at waistband / Hammer loop / Double reinforced crotch seam / Leg pocket with flap and concealed snap fastening, mobile phone pocket and loop for ID-card holder / CORDURA®-reinforced folding rule pocket with tool pocket, pen pocket and button and loop for sheath knife / Reinforced with thigh panels in contrast colour / Pre-shaped knees / CORDURA® reinforced knee pockets with inside opening / Height adjustment for knee pads in knee pocket / CORDURA® reinforced leg ends / Approved according to EN 14404 together with kneepads 124292, EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 9 cal/cm² (see Electric arc table for certified garment combinations for EN 61482-1-2 class 2 and open arc according to EN 61482-1-1), EN ISO 11612 A1 A2 B1 C1 F1, EN 1149-5 and EN ISO 20471 class 2 / Fabric is approved according to EN 13034 / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre. Reinforcement: 79% cotton FR, 20% polyamide, 1% anti-static fibre. Inherent flame protection. In transition to PFAS free.

Weight: 300 g/m².

Color: F171 High vis Yellow/Navy

Size: 34-50



PRO

T3

**CORDURA®
FABRIC**

EN 11612 EN 1149-5 IEC 61482-2 EN 20471 EN 14404

FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04