

PRO Electric Staple Gun R606



Ref: 10643001

Features

- Designed by Ergonomic Design Group.
- Universal magazine for 12-25 mm narrow crown staples and 15-25 mm brads
- Adjustable impact setting through Focused Power – the higher the power, the harder the stapling
- Recoil free action
- Perfect balance
- Supplied with 3.5 m connection lead with moulded plug
- Uses 606 narrow crown staples and No 8 brads
- Applications: Stapling panels, roofing felt, edging and various joinery and furniture industry jobs

Powerful electric staple gun. Excellent staple performance with both hard and soft wood. Perfect balance enables one hand operation leaving the other hand free to work with the materials



Product Information

Narrow crown staple:	606
Brads type:	8
Brads height:	15-25 mm
Max. firing rate/min.:	20 shots
Staple type:	606
Staple height:	12,15,18,23,25 mm
Electrical plug:	Standard European
Width:	75.00
Height:	200.00
Depth:	265.00
Weight:	1550
Material:	Plastic, metal and electronics