

Product Description

The products are green Scotch-Brite™ scouring web rolls of 3 different sizes. 630 and 650 rolls are standard rolls, anyone can cut the desired quantity by himself. 640 roll is already pre-cut, just tear and obtain a sheet.

Note

The scouring web is identical to 3M Scotch-Brite™ 96 pads.

The pads are general purpose cleaning and scouring hand pads, made of high-quality synthetic fiber forming an open textured non-woven web, having abrasive cleaning particles evenly dispersed throughout and bonded to the web with a durable resin.



Product Advantages

- Excellent scouring power
- Flexible, enables to clean corners and borders
- Open web, easy-to-clean
- Does not keep or release harmful ingredients
- Can work in hot water and usual cleaning chemicals
- Very long-lasting
- Consistent performances over the life of the pad

Packaging

6 rolls per case

Product Use

The product can be used wet or dry for scouring cookware pots and pans, for cleaning broilers, and for most equipment in the kitchen.

It is also used for various hand-cleaning jobs in the industry and general building maintenance: scrubbing floors, tables, desks, counters, etc.

The Scotch-Brite™ rolls Ref. 630, 640 and 650 are medium aggressive web and should not be used on surfaces that are scratch-sensitive.

Maintenance

- Rinse the web after each use under tap water.
- If needed, remove deep embedded soil by brushing the pad with a nylon brush, or soak in a cleaning solution to dissolve cooked-on soil.

Product Characteristics

Property	Typical Value
Weight	600 g/sqm
Thickness	8.5 mm
Size	Length 3 m for Ref.630 – Width 158 mm Length 4 m for Ref.640 – Width 200 mm Length 5 m for Ref.650 – Width 158 mm
Printing	White 3M on one side
Color	Dark Green
Aggressiveness*	2.8 g removed
Composition	Nylon fiber Dedicated mineral Polymer resin

*Schiefer test on acrylic plate material (after 5000 revolutions with a new pad)

Country of Origin

Made in 3M Spain in an ISO 9001:2015 and ISO 14001:2015 certified plant.

Health and Safety

When handling any chemical products, read the manufacturer's container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information.

[Follow the link to obtain SDS sheets for 3M products on 3M.com/SDS.](#)

[Follow the link to obtain information about substances of very high concern \(SVHC\).](#)

IMPORTANT! When using any equipment, always follow the manufacturer's instructions for safe operation.

Warranty Information

3M warrants that each 3M product will be free from defects in material and manufacture for the length of the product warranty. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Limited Remedy

This bulletin provides technical information only.

3M recommended product end uses are listed in each 3M Technical Data Sheet. End uses not listed in the applicable 3M Technical Data Sheets are typically not eligible for 3M Warranties. For non-recommended and/or non-warranted end uses or applications, users must test and approve the end uses or applications, assume any associated risks, and acknowledge that 3M has no liability for such end uses or applications. Please contact your 3M representative with any questions about graphic applications, end uses, and warranties.

Limitations of liability

All questions of warranty and liability relating to this product are governed by the terms and conditions of the sale, subject, where applicable, to the prevailing law.

3M and Scotch-Brite are trademarks of 3M Company. All other trademarks are the property of their respective owners.

The use of trademark signs and brand names in this bulletin is based on US standards. These standards may vary from country to country outside the USA.

3M United Kingdom PLC

Commercial Branding and Transportation
Division
Cain Road
Bracknell, RG12 8HT
UK
www.3m.co.uk

3M Ireland Ltd.

The Iveagh Building
The Park, Carrickmines
Dublin 18
Ireland
www.3m.co.uk

© 3M 2024. All rights reserved.