
Epson WorkForce Pro WP-4015 DN

DATASHEET



KEY FEATURES

- Up to 50% lower cost per page*1
- High-speed business-quality results
- Save on paper usage and costs
- Share between multiple users
- Robust and professional white design

We all know how frustrating it is waiting for a print job, even more so when it's only a few pages. That's why Epson created the WorkForce Pro WP-4015 DN printer. Designed to suit the modern office, both inside and out, this is the ultimate professional tool.

Faster printing: It offers a 50% lower cost per page*1 and faster printing*2 for those small print jobs, compared to the top 10 best-selling colour lasers. And when printing double-sided it's twice as fast as the nearest leading competitor*3.

Economical and Ecological: It offers a massive 80% reduction*4 on energy consumption compared to competitive lasers – providing significant cost and environmental savings. Ink cartridges are clean and easy to change and the cartridge is the only part that needs replacing, so the process is hassle-free.

Engineered for Business: A high print resolution of up to 4800x1200dpi means businesses get top-quality prints which are water, smudge, highlighter and fade resistant because they are instantly dry. And the paper capacity of 330 sheets as standard means you won't need to spend valuable time looking after it. Its high-yield, superior quality DURABrite Ultra ink cartridges are low maintenance and offer low-cost printing, producing up to 3,400 pages*10.

Easy to integrate: Network-ready for sharing across workgroups, it comes with USB and Ethernet connectivity.

Print on the move: It comes with Epson Connect*7 to meet all mobile printing needs, enabling users to print from smartphones and tablet PCs.

1. 1 Comparison made against the top 10 A4 colour laser printers and MFPs sold in France, Germany, Italy, Spain, and the UK in Q4 2010 as tracked by IDC. Cost per page is calculated from manufacturers' official list prices for toner cartridges and published yields in France, Germany, Italy, Spain, and the UK as of December 2010

2. 2 Comparison made against the top 10 A4 colour laser printers and MFPs sold in EMEA in Q1 2011 as tracked by IDC. Print speed comparison based on average [Colour/Mono] [Simplex/Duplex] FSOT according to ISO/IEC 24734 test procedure. See www.epson.eu for details and supporting facts

3. 3 When compared to the HP 8500A

4. 4 Comparison made against the top 10 A4 Colour Laser Printers & MFPs sold in France, Germany, Italy, Spain, & UK in Q1 2011 tracked by IDC; power consumption calculated using manufacturers' published data for Print/Average Mode as of July 2011

5. 7 Supports the following languages: English, German, French, Italian, Spanish, Portuguese, Dutch. Requires a wireless connection to the internet. For more information, and supported devices, please visit www.epson.eu

6. 8 Determined in accordance with ISO/IEC 24734 showing the average of ESAT / FSOT from the Office Category Test for default simplex / duplex. For more information visit www.epson.eu

7. 9 Only printing is supported under Windows Server OS, bundled applications are not supported

8. 10 In accordance with ISO/IEEE 24711/24712.

PRODUCT SPECIFICATIONS

TECHNOLOGY	
Nozzle Configuration	152 Nozzles Black, 152 Nozzles per Color
Minimum Droplet Size	3 pl
Ink Technology	Epson DURABrite™ Ultra
Performance	Small Workgroup
PRINT	
Printing Speed	26 Pages/min Monochrome, 24 Pages/min Color
Printing Speed ISO/IEC 24734	16 Pages/min Monochrome, 11 Pages/min Color
Printing Resolution	4,800 x 1,200 DPI
Printing Volume	20,000 Pages per month
CONNECTIVITY	
Interfaces	USB 2.0 Type B, Ethernet interface (100 Base-TX / 10 Base-T)
PAPER SPECIFICATIONS AND SENSORS	
Paper Formats	A4, A5, A6, B5, C4 (Envelope), C6 (Envelope), DL (Envelope), No. 10 (Envelope), 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 13 x 20 cm, 20 x 25 cm, 100 x 148 mm, 16:9, LT, HLT, LGL, User defined
Compatible Paper Weight	64 g/m ² - 256 g/m ²
Duplex	Yes
MP Tray Capacity	80 Sheets Standard, 80 Sheets maximum
Number of paper trays	2
Paper Tray Capacity	250 Sheets Standard, 500 Sheets maximum
GENERAL	
Energy Use	22 Watt (standalone copying, ISO/IEC 24712 pattern), 2.2 Watt (sleep mode), ENERGY STAR® qualified all-in-one
Dimensions	460 mm x 420 mm x 284 mm (Width x Depth x Height)
Weight	10.9 kg
Noise Level	4.8 B (A) according to ISO 7779 pattern with Epson Premium Glossy Photo Paper / Photo RPM mode
Compatible Operating Systems	Mac OS 10.4+, Mac OS 10.5+, Mac OS 10.6+, Windows 7, Windows 7 x64, Windows Server 2003 (32/64bit), Windows Server 2008 (32/64bit), Windows Server 2008 R2, Windows Vista, Windows Vista x64, Windows XP, Windows XP x64
What's in the box	Driver and utilities (CD), Individual Ink Cartridges, Installation/safety manual, Main unit, Power cable, Setup guide, User manual (CD), Warranty document, Wi-Fi/network setup guide
Sound Power	Operation: 6.2 B (A)
Power Supply	110V, 240V
ADDITIONAL FEATURES	
Memory	64 MB Included, 64 MB maximum
Features	Automatic duplex

WHAT'S IN THE BOX

- Driver and utilities (CD)
- Individual Ink Cartridges
- Installation/safety manual
- Main unit
- Power cable
- Setup guide
- User manual (CD)
- Warranty document
- Wi-Fi/network setup guide

LOGISTICS INFORMATION

- SKU
C11CB27301BY
- Barcode
8715946490496
- Dimensions Single Carton
612 x 525 x 485mm
- Weight
15.19kg
- Country of Origin
Indonesia