

# 18518230B300

## PIR movement and presence detector 10 A




This image is for illustrative purposes only and therefore may not represent the exact product code. Colours may vary.

### TECHNICAL DESCRIPTION:

Rilevatore di movimento e presenza, di movimento e presenza, 1 interruttore unipolare, 10 A, Programmazione: Bluetooth, Circuito contatti: contatto libero da potenziale (contatto pulito), Tipo di alimentazione AC, tensione di alimentazione nominale 230 V, funzionamento da 96 a 253 V, potenza nominale 1.5 VA, temperatura ambiente da -10 a +50 °C

[BROWSE PRODUCT PAGE](#)

### Technical Features:

Commercial Description:	Movement and presence detector with Push-in terminals suitable for indoor installation. The Type 18.51 boasts a large detection area (up to 64m2) and is designed to detect both presence, in areas with low activity from occupants, and movement through transit areas or increased activity. The installation, which can be either wall-mounted or recessed, is particularly fast thanks to the cable connection with push-in terminals.
Contact configuration:	1 NO
Dimensions:	84x35.1x84 mm
Manageable with app:	YES
Protection category:	IP 40
Rated contact voltage:	230 V AC
Rated current (contacts):	10 A
Supply:	AC supply version
Type of installation:	Movement and presence detector
Certifications and quality approvals (according to type):	

The information, technical details, data and features contained in this document are subject to change or modification at any time.  
It is for information purposes only and does not form the basis of a contract.

**Need more information?**  
[Contact our sales](#) [Find a dealer](#)