

Mureva BOX - junction box - 10 grommets Ø25 - 150x105x80 mm

ENN05007

! Discontinued on: 2 Mar 2023

EAN Code: 3295150050075

① Discontinued

Main

product range	Mureva BOX
product type	Junction box
quantity per package	1 piece
4	. p.000
Main colour tint	Grey

Complementary

Mounting	Surface	
cable entry	Grommets	
Fixing mode	Screw-fixed: cover	
Inner dimensions	150 x 105 x 80 mm	
number of cable entries	10 diameter: 25 mm	
Material	PP (polypropylene): cover SBS (styrene butadiene styrene): grommet	
Electrical insulation class	Class II conforming to IEC 536	
Height	85 mm	
Width	165 mm	
Depth	125 mm	
Colour tint	Grey (RAL 7035)	

Environment

operating temperature	-2540 °C	
IP-Class	IP55 conforming to IEC 60529	
IK-Class	IK07 conforming to EN 50102	
glow wire temperature	750 °C	
Standards	EN 60670 CE	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	12.000 cm

Package 1 Length	16.300 cm
Package 1 Weight	317.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	36
Package 2 Height	40.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	12.225 kg
Unit Type of Package 3	P12
Number of Units in Package 3	432
Package 3 Height	133.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	156.700 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	3
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No