

### ST44 - BizTex Microporous Shoe Cover

#### Type PB[6] (200 Pairs)

**Collection:** Biztex Micro

**Range:** Hazard Protection

**Shell Fabric:** BizTex Micro, 60g

**Inner Pack:** 25

**Outer Carton:** 200

#### Product information

These protective overshoes are designed for use in all work environments where shoes or floors need protecting. Elastic finish to top of shoe ensures a secure fit. This fabric conforms to EN14126-Biological Protection and EN1149-1 Anti-Static Protection.

##### Biztex Micro

Portwest BizTex™ Micro fabric is a polypropylene substrate to which a laminated microporous polyethylene layer is applied (PP/PE). The outer layer of the fabric prevents the passage of liquid molecules inwards, yet permits the vapour molecules that build up inside to permeate.

#### Hazard Protection

All protective garments under the heading of PPE (Personal Protective Equipment) are controlled in Europe under PPE Regulation EU 2016/425. Portwest has an extensive range of clothing that complies with Category 3 of this regulation.

#### Standards

EN 13034 Type PB [6]

EN 1149 -5



#### Features

- Excellent liquid and particulate barrier protection
- Elasticated cuffs for a secure fit
- Unit of sale is 200 pairs
- CE-CAT III
- CE certified
- UKCA marked
- This product is sold in pairs
- This product is sold in carton quantities



## PRODUCT SPECIFICATION & TECHNICAL DATASHEET

### ST44 - BizTex Microporous Shoe Cover Type PB[6] (200 Pairs) Commodity Code: 6210109800

#### Test House

Centro Tessile Cotoniero e Abbigliamento S.p.A (Notified Body No.: 0624)

Piazza S.Anna 2

, Italy

Cert No: CE 0771200165 \_00 \_ 00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)

SATRA Technology Park

NN16 8SD, United Kingdom

#### Wash Care



#### Carton Dimensions/Weight

| Item    | Colour | Len  | Wid  | Hgt  | Weight(Kg) | Cubic(m <sup>3</sup> ) | EAN13         | GTIN/DUN14     |
|---------|--------|------|------|------|------------|------------------------|---------------|----------------|
| ST44WHR | White  | 43.0 | 28.0 | 35.0 | 4.2200     | 0.0421                 | 5036108203062 | 15036108674012 |