

## Han CGM-P-EXi M32 D 13...20mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7106
Specification	Han CGM-P-EXi M32 D 13...20mm
HARTING eCatalogue	<a href="https://harting.com/19000007106">https://harting.com/19000007106</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-Ex i
Type of accessory	Cable gland

### Version

Field of application	Intrinsically safe electric circuits
----------------------	--------------------------------------

### Technical characteristics

Tightening torque	≤6.5 Nm (depending on the cable and the seal insert used)
Wrench size	42
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M32
Clamping range	13 ... 20 mm
Width across corners	46.8 mm

### Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 5012 (light blue) RAL 9005 (jet black)
Material (seal)	NBR
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	42.1 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140192867
eCl@ss	27140802 Screwed cable gland (explosion-proof, electrical)
ETIM	EC000441
UNSPSC 24.0	39121431