



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 7:55 (UTC)



22213EAE4

Spherical Roller Bearings

Parts Number

22213EAE4C3

Boundary Dimensions

d	65	mm	Bore diameter
D	120	mm	Outside diameter
B	31	mm	Width
r (min.)	1.5	mm	Chamfer dimension

Basic Load Ratings

Cr	221000	N	Basic dynamic load rating
C0r	230000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	4800	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	7500	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	4300	min-1	Grease lubrication
Oil (Oil-bath)	5300	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	74	mm	Diameter of shaft abutment
da (max.)	80	mm	Diameter of shaft abutment
Da (min.)	107	mm	Diameter of housing abutment
Da (max.)	111	mm	Diameter of housing abutment
ra (max.)	1.5	mm	Radius of shaft or housing fillet

Calculation factors

e	0.24	Constant
Y2	4.2	Axial load Factors
Y3	2.8	Axial load Factors
Y0	2.7	Axial load Factors

Mass

Mass approx.	1.51	kg	Mass approx.
--------------	------	----	--------------

