

1993 U-20 G

1/2" Reversible ratchet

with offset handle

Code	ETIM
2746786	EC002218
EAN	UNSPSC
4010886937709	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



1/2" 12,5

Article description

- Used throughout industry and the automotive world - and as well in confined spaces
- Acc. to DIN 3122, ISO 3315
- Handle offset for barely accessible places
- Reduces the risk of injury to the fingers when working on flat surfaces
- Small, drop shaped head for confined areas
- Fine-toothed (60 teeth), with lever change and push-button release
- Return angle 6°
- Non-slip 2-component handle with suspension hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- Vanadium steel 31CrV3, chrome-plated

Article information

Contents [Qty of pieces]	1	Drive connector square [male]	12,5 mm
Net weight [kg]	0,54 kg	Return angle	6°
Total length [mm]	270 mm	Number of teeth	60
Total width [mm]	42 mm	Handle material	2-components
Total height [mm]	40 mm	Ratchet head height	37,5 mm
Surface	chrome-plated	Locking type	Ball locking device
Material	Chrome-vanadium steel 31CrV3	Push button release	yes
Standard	DIN 3122 ISO 3315	Shift type	Changeover lever
Drive connector square [male]	1/2"		