


©1958 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
K	REV PER 063A-0810-00	20 DEC 00	DR/TWA



1. FOR .115 TO .170 WIRE INSULATION DIA.
 2. TONGUE MATERIAL THK. = $.031 \pm .002$
- ⚠ RESTRICTED PART: AMP GREAT BRITAIN LTD. USE ONLY.

QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
—	—	326882-1 ⚠	OBS
100	LOOSE PC, BOX	8-326882-1	
5000	326882 ON TAPE	2-326882-1	BODY & SLEEVE: COPPER (ASTM B 152) TIN PL (MIL-T-10727)
1,000	WIRE TERMINAL	326882	INSULATION: NYLON (MIL-M-20693) TYPE I COLOR: BLUE

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
TOLERANCES ON:
DECIMALS $\pm .008$
ANGLES $\pm 5^\circ$

MATERIAL
SEE TABLE

CONTRACT NO. —

DR. *W. H. Miller* 3-10-71

CHK *W. H. Miller* 3-10-71

APPD *Swable* 3-15-71

REL *H. Young* 3-15-71

DSGN APPD *H. Young*

OTHER APPD

AMP AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

NAME: WIRE TERMINAL
P. I. D. G.-RING TONGUE
WIRE SIZE: 16-14

SIZE	CODE IDENT NO.	NUMBER
A	00779	326882

SCALE: NTS SHEET: OF: CUSTOMER DRAWING