

Datasheet

RS Pro Power Supply Wall Mounting IP66 24Vac 2A

RS Stock No: **916-3908**



Product Details

RS Pro power supply is a reliable and robust IP66 rated device that offers a weatherproof solution to various applications. This 24 V ac, 2 A external power supply offers adjustable glands for both IP and OP wiring to ensure that your application is covered. It is easily replaced, thanks to the intuitive wiring system, along with a mean time before failure (MTBF) of around 50000 h in suitable environments. It comes equipped with various standard safety features such as over voltage, over temperature and short circuit protection.

Features and Benefits

- Current rating of 2 A
- Equipped with various standard safety features such as over voltage, over temperature and short circuit protection
- Meets CE, CEC LEVEL V, EMC and RoHS standards

**Specifications:**

Depth	89.9 mm
Input Voltage	230 V ac
Length	187.2 mm
Maximum Temperature	+40°C
Minimum Temperature	0°C
Mounting Type	Enclosed
MTBF	50000 h
Output Current	2 A
Output Voltage	24 V ac
Power Rating	48 VA
Weight	<1.5 kg
Width	122.2 mm