



R-169

Durable medium-duty impact gloves, offering wearers excellent coverage and cut resistance



Impact

Abrasion Protection



Cut



Medium Duty

Durable medium-duty impact gloves, offering wearers excellent coverage and cut resistance

- **Specialized defenses:** RINGERS® R169 impact protection gloves have been developed with Ringers' F3 Technology™ and a patented TPR (thermoplastic rubber) design, protecting the knuckle, thumb and fingers
- **Enhanced features:** They feature a hook and loop rubber pull tab closure, for a secure cuff with an adaptable fit, while a seamless index finger design further protects areas prone to wear and tear
- **Advanced defenses:** These RINGERS® gloves are rigorously tested, meeting ANSI/ISEA 138-2019 Level 2 for impact protection
- **Improved durability:** Premium synthetic leather has been used in these cut-resistant gloves' palm construction, enhancing durability



Industries

- Manufacturing
- Mining
- Oil and gas
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Utilities

Applications

- Makeup and breakout tools
- Assembly of parts
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- General pumping work
- Handling of tools
- Heavy machine operation
- Maintenance
- Scaffolding
- Loading and hauling
- Primary assembly
- Mounting and dismantling
- Seizing rough blocs and cylinders
- Production line support & maintenance



R-169

Durable medium-duty impact gloves, offering wearers excellent coverage and cut resistance

Key Features

- Optimized TPR design:**Knuckle, thumb and finger protection
- Hook and loop pull tab closure:** For impact gloves with a secure cuff
- ANSI/ISEA 105-2024 CUT A5 and EN ISO F resistance:** For effective defenses

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



GOLD | Top 5%
ecovadis
Sustainability Rating
AUG 2024



EN388: 2016



ANSI/ISEA 138-2019



3X43FP

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R169	Liner Material: HPPE Cuff Style: Adjustable		8, 9, 10, 11, 12, 13	Red	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

