



ENGLISH

Datasheet

## RS Pro Stainless Steel adaptable box 100x100x85

RS Stock No: **121-9693**



### Product Details

RS Pro adaptable box measures 100 x 100 x 85 mm and has high grade 316 stainless steel construction. It is perfect for applications in the food, brewing, dairy, pharmaceutical and chemical industries or anywhere that requires high pressure wash downs. This IP66 rated device has a gasket to give a weatherproof seal for damp conditions. The aesthetically pleasing satin- brushed finishing makes it to fit for architectural applications.

### Features and Benefits

- Satin-brushed stainless steel (316L) construction
- IP66 rated
- ISO conduit threads to BS 4568:1:1970 at both ends



**Specifications:**

Depth	85 mm
Finish	Satin
Height	100 mm
Material	Stainless Steel
Number of Knockouts	4
Width	100 mm