

# JNU01

## JALDOJO SAS

**S3 SRC**  
**EN ISO 20345:2011**  
**35 to 47**



- **Full grain leather / Water-repellent textile**
- **Semelle J-nude PU / TPU**
- **Safety toe cap and midsole no metallic**
- **Antistatic and nonmagnétique**

- ❖ Urban sport style brown and black shoe.
- ❖ Water-repellent full grain upper, pull-up finish and water repellent textile with TPU renfort. Anti-abrasion PU toe protection.
- ❖ Fluorescent markings on the side for increased visibility when doing night work.
- ❖ Breathable upper lining in 3D mesh, with honeycomb structure for improved all-round ventilation of the foot and fast-drying.
- ❖ Vamp lining in non-woven fabric, resists scuffing and acid perspiration.
- ❖ Padded tongue for good instep protection, combined with two side bellows to prevent any dirt from getting into the boots.
- ❖ Padded ergonomic collar in compact flexible foam, lined for extra comfort and better ankle and Achilles tendon protection.
- ❖ Lace up on five pairs of eyelets. Laces : 110 cm.
- ❖ Initial hygiene layer covering the whole surface of the foot, removable, antistatic, antibacterially treated, anatomical and with heel shock absorbers.
- ❖ Ergonomic shoe with **broad synthetic polymer toe cap**, for saving on weight (50% lighter than steel) and removal of perspiration from around the forefoot. Impact resistance to **200 Joules**.
- ❖ New manufacturing **process** : antiperforation inner sole and insert in **FleXtane™ By Jallatte** material, antistatic, **100% composite**. Sewn directly onto the bootstrap and covering **100% of the foot** for all-round protection. **100% composite** materials: lighter than steel, non-magnetic, non-conductive of heat or cold.
- ❖ Heel stiffener to reinforce the heel seat
- ❖ **Innovative soles all in flexibility**, bi-component **Softane/ TPU** for natural foot movement.

<b>Slip resistance tests results</b>	
EN Standard : EN ISO 20345 : 2011	
<b>Requirement SRC (SRA+SRB)</b>	
<b>SRA</b> Test ground : ceramic / lubricant : water and detergent	
On flat <b>0,43</b> (>0,32) – On the heel <b>0,33</b> (>0,28)	
<b>SRB</b> Test ground steel/lubricant : glycerine	
On flat <b>0,22</b> (>0,18) – On the heel <b>0,21</b> (>0,13)	

- Lightweight and durable TPU outsole.
- Confort soles very flexible.
- Independent treads for high stability in every positions.
- Gridded outsole for natural foot movement.
- High slip resistance with the grooves in the front and the back of the sole.



Weight	Gross weight (42) : 1449 g / Net weight (42) : 1262 g		
Size	35 to 39	40 to 45	46 to 47
Packaging	5 pairs	10 pairs	5 pairs
Dimensions carton (mm)	685 x 225 x 345	685 x 440 x 345	685 x 225 x 345
Dimensions box shoe (mm)	340 x 210 x 133		