

Doro Comfort 1015 duo

Cordless DECT phone with answer machine and speakerphone

Doro Comfort 1015 is an elegant cordless phone that brings you lots of functionality with both speakerphone and answering machine. Enjoy long conversations with a handset that is comfortable to hold and also produces good, clear sound thanks to Doro TrueSound quality. Other features include easy to use menus and keys, plus 30 minutes of recording time.

- ✔ Answer machine
- ✔ Speakerphone
- ✔ Loud and clear sound (24dB)



Doro Comfort 1015 duo



Main features

Pre dialling	✓
Speakerphone	✓
Keylock	✓
Call timer	✓
Maximum number of handsets per base	6
Menu navigation	✓
Range indoor (meters)	~50
Range, up to (metres)	300
Out of range warning	✓
Clock	✓
Wake up alarm	✓
GAP compatible	✓

Memories

Redial memory	10
Phonebook positions	50

Handset unit display

Alpha numeric	✓
Backlit display	✓
Display size (H x W mm)	20x35

Sounds & Signals

Monophonic ringtones:	5
Polyphonic ringtones	5
Base ringer	✓
Ringer volume settings except off	5
Ringer off setting	✓

Acoustics

Receiving maximum level (dB(A))	24
HAC (hearing aid compatible)	✓
Volume settings	5

Caller ID

Caller ID memory ¹	20
Caller ID off hook (call waiting) ²	✓
Name display from phonebook	✓
Name display from the network ²	✓
Date & time stamp - internal clock	✓
Date & time stamp - network ²	✓

Answering function

Base handling	✓
Handset handling	✓
Remote access	✓
Memo function	✓
Announce only	✓
Recording time (minutes)	30
Ring count setting	2,4,6,8, call saver

Powering handset unit

Standby time (up to hours)	~100
Talk time (up to hours)	~10
Low battery warning	✓

Technology

DECT	✓
Eco functionality	✓