

## 螺丝刀头 - SF-BIT-TX 15-50 - 1212576

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




螺丝刀头, Torx®, E6.3-1/4" 驱动, 尺寸: TX 15 x 50 mm, 硬化处理, 适用于符合 DIN 3126-F6.3/ISO 1173 标准的手柄

### 优势

- 用于SF-ASD21无线螺丝刀的工具, 多种型号

### 关键商业数据

包装单位	5 STK
最小订货量	5 STK
GTIN	 4 046356 590112
GTIN	4046356590112
Sales Key	BG3149

### 技术数据

#### 尺寸

长度 (b)	50 mm
刀片高度	50 mm

#### 概述

颜色	银色
类型	Torx
标识材料	合金工具钢
测试标准	DIN 3126

#### 标准和规范

测试标准	DIN 3126
------	----------

#### Environmental Product Compliance

California Proposition 65	加州65提案的更多信息, 请访问制造商声明下的“下载区”
---------------------------	------------------------------

### 产品图

# 螺丝刀头 - SF-BIT-TX 15-50 - 1212576

图画文字



## 分类

eCl@ss

eCl@ss 10.0.1	21044290
eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402
eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21044290
eCl@ss 8.0	21044202
eCl@ss 9.0	21044290

ETIM

ETIM 4.0	EC002117
ETIM 5.0	EC002117

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

## 认证

认证

认证

EAC

防爆认证

## 认证详情

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------

