

5957VI

Assortment of 162 tools

Industrial maintenance

		art.
	059571005	5957VI



- n. 6 **31/SP6**: pin punches Ø 2 - 3 - 4 - 5 - 6 - 8 mm
- n. 6 **38/SP6**: 2 drift punches, 1 centre punch, 3 flat chisels with metal holder
- n. 18 **42**: combination wrenches
6-7-8-10-11-12-13-14-15-16-17-19-21-22-24-27-30-32 mm
- n. 12 **55/S12X**: double open end wrenches 6x7 ÷ 30x32 mm
- n. 8 **96T/S8**: offset hexagon key wrenches 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
- n. 8 **97TX/SC8**: offset key wrenches, for Torx® head screws ⌘ T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
- n. 1 **111E**: Adjustable wrench 250 mm
- n. 13 **920B/SB13**: 1/2" square drive bi-hex sockets with rail ○ 10÷22 mm
- n. 8 **920B/SB8**: 1/2" square drive bi-hex sockets with rail ○ 23÷32 mm
- n. 4 **920LP**: 1/2" socket drivers for slotted head screws ● 1,2x6,5 - 1,2x8 - 1,6x9 - 2x12 mm
- n. 3 **920PH**: 1/2" socket drivers for Phillips® screws ⌚ PH2 - 3 - 4
- n. 1 **920/21**: 1/2" drive extension bar 125 mm
- n. 1 **920/22**: 1/2" drive extension bar 255 mm
- n. 1 **920/25**: 1/2" drive universal joint
- n. 1 **920/42**: 1/2" drive sliding T-handle
- n. 1 **920/55**: 1/2" reversible ratchet ⌚
- n. 1 **963**: pry bar
- n. 2 **1032**: circlip pliers straight, internal ○ 140 - 180 mm
- n. 2 **1034**: circlip pliers bent, internal ○ 130 - 170 mm
- n. 2 **1036**: circlip pliers straight, external ● 140 - 175 mm
- n. 2 **1038**: circlip pliers bent, external ● 135 - 175 mm
- n. 1 **1048N**: slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 1 **1051**: self locking pliers, double adjustment
- n. 1 **1084BM**: Heavy-duty diagonal cutting nippers ⌘ 160 mm
- n. 1 **1092V**: toggle lever assisted end cutting nippers ⌘ 180 mm
- n. 1 **1112**: tin snips 250 mm
- n. 1 **1114**: tin snip, straight narrow blades 250 mm
- n. 1 **1128BMX**: electrician's scissors, straight blades 147 mm
- n. 1 **1150BM**: combination pliers bright chrome-plated, bi-material handles = 180 mm
- n. 1 **1166BM**: Extra-long needle nose pliers ● 160 mm
- n. 1 **1168BM**: Extra-long bent needle nose pliers ● 160 mm
- n. 7 **1260**: screwdrivers for slotted head screws ● 2,5x50 - 3x75 - 4x100 - 5,5x125 - 6,5x150 - 8x200 - 10x200 mm
- n. 4 **1262**: screwdrivers for cross head Phillips® screws ⌚ PH0x60 - PH1x80 - PH2x100 - PH3x150 mm
- n. 3 **1370**: engineer's hammer 300 - 600 - 1000 g
- n. 1 **1390**: soft face hammer Ø 35 mm
- n. 1 **1692**: measuring tape 5 m