



### Main

Range	PowerLogic
Product name	CT
Product or component type	Current transformer
Secondary current	5 A
Accuracy class	Class 3 at 1 VA
[In] rated current	40 A

### Complementary

Current transformer type	Tropicalised for cable
Current transformer ratio	40/5
[Ith] conventional free air thermal current	2.4 kA
Dynamic withstand current	2.5 Ith
Maximum safety factor	5
[Ue] rated operational voltage	< 720 V AC 50/60 Hz
[Ui] rated insulation voltage	3 kV
Mounting mode	By screws Clip-on
Mounting support	Mounting plate DIN rail
Width	44 mm outside:
Height	65 mm outside:
Depth	30 mm frame: 37 mm total:
Diameter	21 mm
Net weight	0.19 kg
[Uimp] rated impulse withstand voltage	3 kV
Electrical insulation class	Class B

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Cable outer diameter	21 mm
Sealing	With

## Environment

Standards	VDE 0414 IEC 61869-2
Product certifications	CE
IP degree of protection	IP20
Relative humidity	0...95 %
Ambient air temperature for operation	-25...60 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins