


Data sheet

Commercial Art.No.: 76.350.0760.5

hood MIN GOT GA 7 M20 25 P5

Hood revos MINI made of Plastik, ankled with cable gland M20 (IP65), low version



Technical data

general

housing material	plastic
color	white
surface	untreated
degree of protection (IP)	IP65
UV resistant	yes
flammability class of insulation material acc. with UL94	V0
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	3
model of the housing	male
locking mechanism	single locking lever
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	48 mm
width	36 mm
height	48 mm

classification

ECLASS 11	
ECLASS 8.1	27440202
ETIM 9.0	EC000437
ETIM 8.0	EC000437
ETIM 7.0	EC000437
ETIM 6.0	EC000437
ETIM 5.0	EC000437
ETIM 4.0	EC000437
ETIM 3.0	EC000437

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant