



### Main

Range of product	Mini Pragma
Product or component type	Base
Accessory / separate part category	Enclosure accessory
[In] rated current	63 A
Number of horizontal rows	2
Number of 18 mm modules per row	12
Terminal block function	Without

### Complementary

Enclosure mounting	Flush
Total number of 18 mm modules	24
Cable entry	Pre-cutted holes
Enclosure material	Back part: technoplastic
Width	270 Mm wall:
Height	353 Mm wall:
Depth	80 Mm wall: 18 Mm outside: 98 Mm total:

### Environment

Standards	EN 50102 IEC 60695-2-11
Fire resistance	Back part: 650 °C
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	664 G
Package 1 Height	8 Cm
Package 1 width	27 Cm
Package 1 Length	35.3 Cm
Unit Type of Package 2	BB1
Number of Units in Package 2	7

Package 2 Weight	4.748 Kg
Package 2 Height	30 Cm
Package 2 width	52 Cm
Package 2 Length	40 Cm
Unit Type of Package 3	P12
Number of Units in Package 3	112
Package 3 Weight	87.97 Kg
Package 3 Height	120 Cm
Package 3 width	80 Cm
Package 3 Length	120 Cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**