



**Part Number :** 1053860004  
**Product Description :** Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 1.0µm Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)  
**Series Number :** 105386  
**Status :** Obsolete  
**Product Category :** Connector Accessories



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
--------	----------

Category	Connector Accessories
Series	105386
Description	Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 1.0µm Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)
Component Type	Clip
Product Name	Spring Clip
UPC	889056283656

## Electrical

Current - Maximum per Contact	1.5A
-------------------------------	------

## Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Material - Metal	Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.023/g
Packaging Type	Embossed Tape on Reel
Plating min - Mating	1.016µm
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Solder