

Specifications

Eaton EVBAF332X

Eaton Basic G4 Rack PDU, 0U, 39U, IEC-60309 input, 3m cord, 3ph, 22kW, 32A, 415/240V, 42 outlets (24)C13, (18)C39



General specifications

PRODUCT NAME	Eaton Rack PDU G4
CATALOG NUMBER	EVBAF332X
MODEL CODE	PDU G4 BA 0U 309 32A 3P 24xC13,18xC39
EAN	3553340697166
PRODUCT LENGTH/DEPTH	1730 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	52 mm
PRODUCT WEIGHT	4.9 kg
COMPLIANCES	CB LVD Directive RoHS Directive WEEE Directive Packaging Directive
CERTIFICATIONS	IEC 62368-1 EN IEC 63000 CE EAC UKCA Cm Ukr



Powering Business Worldwide

Electrical input

INPUT CONNECTION	IEC-60309 32A 3Ph
WATTAGE	22 kW max
AMPERAGE RATING	32 A
INPUT VOLTAGE	240/415V
PHASE	Three-phase
CIRCUIT BREAKER	(6) single-pole
FREQUENCY RATING	50/60 Hz
CORD LENGTH	3m

Technology & communications

TYPE	Basic Rack PDU
OUTLET CONTROL	No

SPECIAL FEATURES

- Versatile C39 outlet supports C14 or C20 power cord plug
- High retention outlets designed to securely fit standard power cords and support P-Lock power cords
- Color-coded outlet banks and corresponding circuit breakers

ETHERNET INTERFACE	No
SERIAL INTERFACE	No
SNMP	No
COMMUNICATION	No
MASS CONFIGURATION	No

Resources

BROCHURES	Rack PDU G4 Brochure EN
DECLARATIONS OF CONFORMITY	EU declaration of conformity Rack PDU G4

Electrical output

OUTLETS	(24) C13, (18) C39
NUMBER OF OUTPUTS C13	24
NUMBER OF OUTPUTS C19	18
NUMBER OF OUTPUTS (OTHER)	18
NUMBER OF OUTLETS WITH EARTH PIN	42

Additional specifications

OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)
------------------------------	---------------------------

ACCESSORIES

- Rack PDU
- Rack mounting accessories
- Quickstart guide
- Safety Instructions

MATERIAL	Aluminium
COLOR	Black

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

