

Price* : 86.51 GBP



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Range compatibility	Prisma P Prisma G
Power range	90 W
Input voltage	110...250 V AC 50/60 Hz

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Product certifications	UL VDE
Material	Extruded aluminium for body
Height	200 mm
Width	85 mm
Depth	65 mm
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
