

Features

- Multi-language support
- Free Type and Windows Font support
- Defining user image library
- Simulation feature
- C/C++ real-time programming
- 260K Display colours
- 480x272 Display resolution

RS PRO 4.3" HMI Panel

RS Stock No.: 0315659



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

BACNET MSTP,
MODBUS-RTU / -ASCII (Master / Slave) communication,
Compatible with OMRON Host Link, DELTA DVP Series PLCs.

General Specifications

CPU	ARM Cortex-A Series
Flash Memory	8GB eMMC
RAM	512 MB DDR3 SDRAM
Backlight Life	50000 hours
Luminance (Cd/m2)	530

Mechanical Specifications

Device Dimensions	153x105x40.5mm
Panel Cut-Out	139x94mm
Weight	350gr

Electrical Specifications

Operation Voltage	18...30Vdc
Power Consumption	5W (4.3")
RTD Battery / Life	CR2023 Button Cell Lithium bat. / 3V - 5 years

Protection Category

Protection Class	IP65
------------------	------

Approvals

Compliance/Certifications	CE Certificate
---------------------------	----------------

Electrical Connection

