

# 83 61 010

## Pipe Wrench S-Type with fast adjustment



- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- Guard prevents operators' fingers being pinched
- Maximum load capability thanks to completely hardened handles
- High wear resistance due to the additionally hardened teeth
- Chrome vanadium electric steel, forged, multi stage oil-hardened



<b>Article No.</b>	83 61 010
<b>EAN</b>	4003773078876
<b>Pliers</b>	grey powder-coated
<b>Handles</b>	plastic coated
<b>Clamping width mm</b>	42
<b>Capacities for pipes (diameter) Ø mm</b>	42
<b>Capacity for pipes, inches (diameter) Ø Inch</b>	1 5/8
<b>Inner diameter, inches Inch</b>	1
<b>Capacities for nuts mm</b>	42
<b>Inside dia. mm</b>	25,0
<b>Length mm</b>	330
<b>Net weight g</b>	955



*technical change and errors excepted*

