

OC 2329843

Kitting Order Description: Res Kit 0805 1% (122 Values)

Style: ALBUM KIT

Part Number : 1625873-5

Quantity per

Value: 50 pcs

Page: 1 of 1

| No. | Value | Part No |
|-----|-------|---------|
| 1   | 0R0   |         |
| 2   | 10R   |         |
| 3   | 11R   |         |
| 4   | 12R   |         |
| 5   | 13R   |         |
| 6   | 15R   |         |
| 7   | 16R   |         |
| 8   | 18R   |         |
| 9   | 20R   |         |
| 10  | 22R   |         |
| 11  | 24R   |         |
| 12  | 27R   |         |
| 13  | 30R   |         |
| 14  | 33R   |         |
| 15  | 36R   |         |
| 16  | 39R   |         |
| 17  | 43R   |         |
| 18  | 47R   |         |
| 19  | 51R   |         |
| 20  | 56R   |         |

| No. | Value | Part No |
|-----|-------|---------|
| 21  | 62R   |         |
| 22  | 68R   |         |
| 23  | 75R   |         |
| 24  | 82R   |         |
| 25  | 91R   |         |
| 26  | 100R  |         |
| 27  | 110R  |         |
| 28  | 120R  |         |
| 29  | 130R  |         |
| 30  | 150R  |         |
| 31  | 160R  |         |
| 32  | 180R  |         |
| 33  | 200R  |         |
| 34  | 220R  |         |
| 35  | 240R  |         |
| 36  | 270R  |         |
| 37  | 300R  |         |
| 38  | 330R  |         |
| 39  | 360R  |         |
| 40  | 390R  |         |

| No. | Value | Part No |
|-----|-------|---------|
| 41  | 430R  |         |
| 42  | 470R  |         |
| 43  | 510R  |         |
| 44  | 560R  |         |
| 45  | 620R  |         |
| 46  | 680R  |         |
| 47  | 750R  |         |
| 48  | 820R  |         |
| 49  | 910R  |         |
| 50  | 1K0   |         |
| 51  | 1K1   |         |
| 52  | 1K2   |         |
| 53  | 1K3   |         |

| No. | Value | Part No |
|-----|-------|---------|
| 61  | 3K0   |         |
| 62  | 3K3   |         |
| 63  | 3K6   |         |
| 64  | 3K9   |         |
| 65  | 4K3   |         |
| 66  | 4K7   |         |
| 67  | 5K1   |         |
| 68  | 5K6   |         |
| 69  | 6K2   |         |
| 70  | 6K8   |         |
| 71  | 7K5   |         |
| 72  | 8K2   |         |
| 73  | 9K1   |         |

|    |     |  |
|----|-----|--|
| 54 | 1K5 |  |
| 55 | 1K6 |  |
| 56 | 1K8 |  |
| 57 | 2K0 |  |
| 58 | 2K2 |  |
| 59 | 2K4 |  |
| 60 | 2K7 |  |

|    |     |  |
|----|-----|--|
| 74 | 10K |  |
| 75 | 11K |  |
| 76 | 12K |  |
| 77 | 13K |  |
| 78 | 15K |  |
| 79 | 16K |  |
| 80 | 18K |  |

| No. | Value | Part No |
|-----|-------|---------|
| 81  | 20K   |         |
| 82  | 22K   |         |
| 83  | 24K   |         |
| 84  | 27K   |         |
| 85  | 30K   |         |
| 86  | 33K   |         |
| 87  | 36K   |         |
| 88  | 39K   |         |
| 89  | 43K   |         |
| 90  | 47K   |         |
| 91  | 51K   |         |
| 92  | 56K   |         |
| 93  | 62K   |         |
| 94  | 68K   |         |
| 95  | 75K   |         |
| 96  | 82K   |         |
| 97  | 91K   |         |
| 98  | 100K  |         |
| 99  | 110K  |         |
| 100 | 120K  |         |

| No. | Value | Part No |
|-----|-------|---------|
| 101 | 130K  |         |
| 102 | 150K  |         |
| 103 | 160K  |         |
| 104 | 180K  |         |
| 105 | 200K  |         |
| 106 | 220K  |         |
| 107 | 240K  |         |
| 108 | 270K  |         |
| 109 | 300K  |         |
| 110 | 330K  |         |
| 111 | 360K  |         |
| 112 | 390K  |         |
| 113 | 430K  |         |
| 114 | 470K  |         |
| 115 | 510K  |         |
| 116 | 560K  |         |
| 117 | 620K  |         |
| 118 | 680K  |         |
| 119 | 750K  |         |
| 120 | 820K  |         |

| No. | Value | Part No |
|-----|-------|---------|
| 121 | 910K  |         |
| 122 | 1M0   |         |