



# SPECIFICATION

Stock No: 2006749



## High CRI Rechargeable Pocket Floodlight

### Technical Data

650 Lumen high quality 7W COB LED  
High CRI 96+  
3 colour temperatures - CCT: 2700k / 4500k / 6500k  
Super tough nylon construction with TPE handle grip  
360-degrees rotating stand/handle  
Strong magnets within the handle  
Useful battery level and charge indicator lights  
1m USB Type-C charging cable included  
IP65 dust & water resistant  
IK07 Impact resistant  
2m Drop proof

**Operating Temperature:** -20° to +50°

**Product Size:** 93 × 88.5 × 30 mm

**Product Weight:** 243g

**Battery:** Rechargeable high quality 3.7v 2600mAh Li-ion battery

**Charging time:** approx 4 hours

### Runtimes

High - 650 Lumen (2700k / 4500k / 6500k) - 2 hours

Low - 300 Lumen (2700k / 4500k / 6500k) - 4.5 hours

### Operation

Press the Switch on the back of the Light to cycle through the 3 colour temperatures:

Sequence:- 2700k > 4500k > 6500K

When ON in any colour, press and hold the switch to dim to the low setting.



**650 LUMENS**



**2 Brightness Settings**



**360° Adjustable Handle**



**USB-Type-C Rechargeable**



**USB Charging Cable Inc.**

