



Datasheet CCTV UK PSU Wall Mounting Range

ENGLISH



Features

- Universal AC Input
- Fixed UK AC Mains Lead
- Small & Compact Design
- Built-in wall mounting tabs
- Over Voltage, Short Circuit & Over Temp. Protections
- ErP Level V
- RoHS Compliant
- MTBF >50,000 hours

RS Stock Number	Manufacturers P/N	Output Voltage	Output Current (Min)	Output Current (Max)	Power (Watts)	Line Regulation	Voltage Tolerance	Ripple & Noise (mV- p-p)
8280052	T3717ST	12Vdc	0A	3.5A	42W	+/-1%	+/-0.6V	120mV
8280055	T3718ST	24Vdc	0A	1.75A	42W	+/-1%	+/-0.6V	240mV

Input

- Rated Input 100-240Vac
- Rated Input Frequency 50-60Hz
- Input Current 1.5A
- Inrush Current 75A at 230Vac
- Efficiency 75%
- 2M UK Mains Lead with Plug

Output

- 1.8M Cable
- Straight 2.1C+ve Connector

Environmental

- Operating Temperature 0°C to 40°C
- Storage Temperature -20°C to 75°C
- Operating Humidity 20% to 90%
- Storage Humidity 0% to 90%

Casing

- Dimensions 114mm x 32mm x 51mm
- Weight 240g (approx.)

