



10 mm 1/4" impact socket deep - 1 pc

SHOCKWAVE™ IMPACT DUTY IMPACT SOCKETS

- SHOCKWAVE™ IMPACT DUTY steel (Chrome-Molybdenum) is high quality alloy steel which provides ultimate strength and durability.
- Best fitting thanks to 6 gripping points.
- Non-slip hex geometry to prevent socket and fastener rounding.
- Deep wall construction provides clearance for protruding bolts.
- Stamped and ink filled diameter markings and laser etched part number for wear resistance.
- Dual hole design and groove for security accessories.



Article Number	4932480259
For anchor thread size	M6
Outside diameter (mm)	13.8
Pack quantity	1
Size AF (across flats) (mm)	10
Tool reception	1/4" square
Total length (mm)	50
Working depth (mm)	4.6
Working length (mm)	4.6