

370033162

# Stainless steel industrial enclosure IGSN A4 300 x 300 x 167 mm

Stainless steel industrial enclosure IGSN A4 300 x 300 x 167 mm

Drawing 3D Data

## Technical data

| | |
|---|---|
| Height | 300 mm |
| Width | 300 mm |
| Depth | 167 mm |
| Material | Stainless Steel |
| Material quality | 1.4404/316L |
| Ingress protection | IP66 |
| Degree of protection norm | EN 60529 |
| Impact strength | IK09 |
| temperature min. | -60 °C |
| temperature max. | 175 °C |
| Seal material | VMQ-(silicone) |
| Flame spread, sideways | HL 3 |
| Rate of head dispersion | HL 3 |
| Smoke gas concentration | HL 3 |
| Other versions on request | EMV |
| Approvals | LR (Lloyd's Register), UL (508A) |

## Commercial data

| | |
|---|---|
| Country of origin | IN |
| Order unit | 1 Piece |
| Customs tarif number | 85369095 |
| Weight | 4.59 kg |
| GTIN | 4057624608514 |


## ETIM classification

| | |
|---|---|
| ETIM 8 | EC000058 |


ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de


## Accessories



100110440
Mounting plate for 37.3030xx




100614360
DIN rail 35/7,5 for 37.301508



100620210
Earth rail for 37.301508



100681210
Protective conductor busbar for 34.30xxx /xx.0033xx



370100030
Flange size 3 - 130x260x3



371050000
Stainless steel external mounting brackets



379900010
Mounting set for Stainless-steel enclosures