



Main

Range	Exiway
Product name	Exiway Easyled
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard
Supply	Non-maintained
Number of batteries	1 x 4.8 V 0.8 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	LED integral LED 11 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Range compatibility	Remote control
[Ue] rated operational voltage	220...230 V AC 50/60 Hz
Power consumption in VA	2.5 VA
Power consumption in W	1.6 W
Current consumption	10 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 H
Luminous flux	170 Lm
Type of glass	Serigraphed transparent glass
Material	Housing: plastic Cover: plastic
Device mounting	Surface ceiling Flush false ceiling Flush wall Surface wall
Height	116 Mm
Width	292 Mm
Depth	37 Mm
Net weight	0.48 Kg

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	ENEC
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	525 G
Package 1 Height	3.8 Cm
Package 1 width	11.7 Cm
Package 1 Length	29.3 Cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**