

Features

- Auto-sync laser function
- Light intensity 9,000 LUX
- Quartz accuracy flash control
- Ergonomic one-handed operation
- Switchable between standard and professional modes
- Protective holster
- AA Battery powered

RS PRO Stroboscopes

RS Stock No.: 254-2485



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS PRO strobe pocket LED LASER

This high-quality digital instrument is battery powered and can be used for measuring rotational speed as well as carrying out inspections of machinery. The LED light provides a powerful 9000 LUX beam that can be varied in flash rate from 30 to 999,999 fpm.

By means of a built in reflective laser beam, the pocketLED LASER offers the possibility to automatically set the flash rate and thus let moving parts appear optically "frozen". The unit can also be used as a laser tachometer with flash function disabled to accurately measure the rotating speed of any target.

The RT LED Strobe also has the facility to adjust flash duration to ensure a crisp image and includes time delay for greater flexibility and best noted accuracy is 0.02%.

General Specifications

Brand	RS PRO
Best Accuracy	0.02%
Sample Time	0.025° - 6.000° / 1 - 1,000 μ s
Flash Colour	LED WHITE
Dimensions	191 x 82 x 60mm
Weight	930g (including case)
Maximum Operating Temperature	45 °C / 113 °F
Maximum Speed	999
Minimum Flash Rate	30 flashes per minute
Minimum Operating Temperature	0 °C / 32 °F
Power Source	3 x AA Batteries (Supplied)

Protection Category

IP65

Approvals

Declarations	MFR Declaration of Conformity
--------------	-------------------------------