



Price\* : 11.29 GBP



### Main

|                            |   |
|----------------------------|---|
| Range of product           | OsiSense XC   |
| Series name                | Special format  |
| Product or component type  | Limit switch lever  |
| Device short name          | ZC2J  |
| Product compatibility      | XC2J  |
| Associated head            | ZC2JE01<br>ZC2JE02<br>ZC2JE03<br>ZC2JE04<br>ZC2JE05<br>ZC2JE06<br>ZC2JE07 |
| Movement of operating head | Rotary  |
| Type of operator           | Roller lever spring return metal (-)                                      |
| Type of approach           | Lateral approach  |

### Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | Without    |

### Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | 10...120 °C for high temperature<br>-40...70 °C for low temperature<br>-25...70 °C for standard environment |
| Ambient air temperature for storage   | -40...70 °C for low temperature<br>10...120 °C for high temperature<br>-40...70 °C for standard environment |
| Environmental characteristic          | High temperature<br>Low temperature<br>Standard environment   |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1014 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product end of life instructions | Need no specific recycling operations   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|