

## 251A - PRECISION SLEEVED DRIFT PUNCHES | 251A.1



### Description

- The centre slides within a guide to prevent distortion, even in smaller sizes.
- Shank hardened to 52 to 57 HRc.
- Zinc-plated body, burnished body.

### Information

A [mm] 0,9

d [mm] 3

L [mm] 70

L1 [mm] 14

[g] 5

[kg] 0,005

