



S560MH

1/4" and 1/2" Square Drive Socket Set with Metric Bi-Hex Profile and Metal Handle Ratchet - 56 Pcs



PRODUCT DETAILS

- 12-Piece 1/4" bi-hex sockets 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12 and 13 mm
- 10 1/4" bi-hex deep sockets 4, 5, 6, 7, 8, 9, 10, 11, 12 and 13 mm
- 13-Piece 1/2" bi-hex sockets 10, 11, 12, 13, 14, 15, 17, 19, 22, 24, 27, 30 and 32 mm
- Three 5/16" TORX® bits: T45, T50 and T55
- One 1/4" magnetic adaptor
- Two 1/4" extension bars, 50 mm/2" and 100 mm/4"
- One 1/4" sliding T-bar, 125 mm/5"
- One 1/4" universal joint
- One 1/4" spinner with metal handle
- One 1/4" bit holder
- One 1/4" bit adaptor
- 1/2" extension bars, 125 mm/5"
- 1/2 offset handle 8178
- One 1/2" spark plug hex socket, 21 mm (13/16")
- One 1/2" T-adaptor for slidign T-handle
- One 1/2" x 5/16" bit holder
- Three hexagon L-keys: 1.5, 2 and 2.5 mm
- One 1/4" metal handle ratchet, quick release, 60 teeth/6° action angle
- One 1/2" metal handle ratchet, quick release, 60 teeth/6° action angle
- Micro Matte finish
- High-performance alloy steel
- Less wear and damage to fastener thanks to Dynamic-Drive™ profile sockets
- Quick socket release button on ratchet
- Case: High density polythene (HDPE)
- Standards: ISO 1174 and DIN 3120

PRODUCT ATTRIBUTES

| Product |  |  |  |  |
|---------------|---|---|---|---|
| S560MH | 375 mm | 215 mm | 100 mm | 5025 g |

Follow the Fish!

