
PRODUCT-DETAILS

TY51M-2

CABLE TIE 18LB 4 RED ID 1X.313 MA



General Information

Extended Product Type	TY51M-2
Product ID	7TAG009510R0047
EAN	5414363065197
Catalog Description	CABLE TIE 18LB 4 RED ID 1X.313 MA
Long Description	Identification Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 91.44mm (3.6 Inches), Width of 2.36mm (0.093 Inches), Thickness of 25.4mm (1.0 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Marking Pad Size of 25.4mm (1.0 Inches) x 7.95mm (0.313 Inches)

Ordering

EAN	5414363065197
UPC	786210875415

Dimensions

Product Net Width	0.093 in 2.36 mm
Product Net Depth / Length	3.6 in 91.4 mm

Container Information

Package Level 1 Units	500 piece
-----------------------	-----------

Package Level 1 Width	3.6 in 91 mm
Package Level 1 Height	8.2 in 208 mm
Package Level 1 Depth / Length	4.9 in 124 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	12.4 in 315 mm
Package Level 2 Height	3.3 in 84 mm
Package Level 2 Depth / Length	15 in 381 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Red
Effective Date	19671108
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Identification
Standards	UL E49405
Tensile Strength	18 lb 80 N
Thickness	0.038 in 0.97 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY51M-2
Instructions and Manuals	TY51M-2

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5040 >> I.D. Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

