




Clamp: Phosphor bronze, Ni plated



	linear dimension				fillet	chamfer		 short angle sid									
variable range	to 6	over 6 to 30	over 30 to 120	over 120 to 480	all	to 6	over 6 to 10	to 10	over 10 to 50	over 50 to 120	over 120 to 200	all	to 5	over 5 to 30	over 30 to 120	over 120 to 200	
tolerance	± 0.1	± 0.2	± 0.3	± 0.5	± 0.9	± 0.2	± 0.5	± 1	1°	30'	20'	10'	0.5	0.025	0.06	0.12	0.4

UNITS	mm	SIZE	A4	SCALE	FIRST ANGLE PROJECTION 	
					NAME	20.1550MF/XX-E 21.1550MF/XX-E