

# 12Vmax Angle Drill CXT

## DA333DZ

DA333D is a 12V max Angle Drill powered by CXT slide battery, and is the ideal machine for working in confined and hard-to-reach spaces.

10.8V Angle Drill CXT



### TECHNICAL SPECIFICATIONS

Voltage	12 v
No Load Speed	0 - 1,100 rpm
Battery Type	Lithium-ion
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	70 dB(A)
Body only machine	✓
Net weight	1.2 - 1.4 kg
Battery Quantity (2.0Ah)	0
Capacity in Steel	10 mm
Capacity in Wood	12 mm
Chuck Capacity	0.8-10 mm
Vibration: Drilling into metal	3.0 m/sec <sup>2</sup>

### USER BENEFITS

- Keyless Chuck
- Electric brake
- LED job light
- Variable speed control trigger.
- Forward / reverse rotation
- Compact head size for convenience when operating in tight spaces
- Ergonomically designed handle with soft grip.
- Large Switch Lever
- Belt clip

[Link to product - www.makita.com](http://www.makita.com)



# RELATED PRODUCTS

(Recon

## ■ OTHER