

**Clevis foot**  
**CRLMC-40**  
Part number: 197321



 [General operating condition](#)

**Data sheet**

| Feature                        | Value                                                                     |
|--------------------------------|---------------------------------------------------------------------------|
| Size                           | 40                                                                        |
| Based on standard              | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Mounting position              | optional                                                                  |
| Corrosion resistance class CRC | 4 - Very high corrosion stress                                            |
| LABS (PWIS) conformity         | VDMA24364-B2-L                                                            |
| Ambient temperature            | -40 °C ... 80 °C                                                          |
| Product weight                 | 144 g                                                                     |
| Note on materials              | RoHS-compliant                                                            |
| Material mounting              | Electropolished<br>High-alloy steel                                       |
| Material bearing               | Polymer                                                                   |