

FEATURES

-
-
-
-
-

RS PRO Vices

RS Stock No.: 554-425

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Please introduce the product with relevant details stating:

General Specifications

Vice Type	Bench Vice; Drill Vice; Milling Vice
Colour	Grey; Blue
Number of Sheet per Pack	4; 1
Construction	Aluminium steel and the base cast iron
Base Type	Fixed; Swivel
Applications	

Mechanical Specifications

Jaw Opening	70mm
Jaw Width	50mm
Jaw Depth	38mm
Jaw Height Capacity	31mm
Jaw Height from Base	50mm
Overall Length with Jaws Closed	260mm
Overall Length with Jaws Fully Closed	320mm
Clamping Slot Width	11.5mm
Maximum Clamping Force	2000N
Rotating Vice Head	360°
Mounting	Bolts; Clamp; G Clamp; Interchangeable Screw; Screw
Weight	1.45kg

Classification

eCl@ss Version	
UNSPSC Version	

Approvals

Declarations	
---------------------	--