



APC Replacement Battery Cartridge #106
Part Number: APCRBC106



Batteries & Runtime	
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	2 - 5
RBC™ Quantity	1
Physical	
Net Weight	2.50 KG
Maximum Height	48.00 mm
Maximum Width	102.00 mm
Maximum Depth	140.00 mm
Shipping Weight	2.77 KG
Shipping Width	175.00 mm

Shipping Height	89.00 mm
Shipping Depth	213.00 mm
Color	Black
Units per Pallet	150.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	0 - 40 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-3000 meters

Conformance

Standard Warranty	1 year repair or replace
-------------------	--------------------------

Sustainable Offer Status

RoHS	Compliant
PEP	Available in Documentation tab
EOL	Available in Documentation tab

*