

TW50-H Form 6 G 1/2 B G 1/2 female U1=232 mm 1.4571

Doigt de gant foré dans la mas

Item number: 3909203

Quantity: 1 pcs.

Order code: TW50-H-L5-GD-TD-0232-N-ZZ-Z-Z ZI0260Q9Z

Overview: TW50-H Form 6 G 1/2 B G 1/2 female U1=232 mm 1.4571

Process thread [P or E]: G 1/2 B

Connection to thermometer [N]: G 1/2 female

Insertion length [U1]: 232 mm

Bore size [B or d1]: 0.354 inch (9.0 mm)

Specifications according to data sheet: TW 95.50

Details:

Doigt de gant foré dans la mas

ZUBEHÖR Doigt de gant foré dans la masse CrNi-Stahl 1.4571 G1/2AxG1/2A 232 mm 8 mm

Thermowell TW50, solid machined DIN 43772 (Form 6,7,9)

Specifications according to data sheet: TW 95.50

Thermowell style: Form 6 (female thread to thermometer, straight process thread)

Material: Stainless steel 1.4571

Process thread [P or E]: G 1/2 B

Connection to thermometer [N]: G 1/2 female

Insertion length [U1]: 232 mm

Bore size [B or d1]: 0.354 inch (9.0 mm)